



Pre-Designed Turbocompressors (Blowers)


The comprehensive product range from 600 up to 600,000 m³/h

Answers for energy.

SIEMENS

Pre-designed turbocompressors

The comprehensive Siemens product range from 600 up to 600,000 m³/h



STC-SOF

(formerly known as SFO or SFP series)

from 15,000 up to 600,000 m³/h


The STC-SOF (SFO/SFP) is a single stage centrifugal compressor with open-form, overhung impeller. The rotor is supported in a separate bearing pedestal. If required, this machine type is designed according to API-standards.

Technical data

- Flow rates from 15,000 up to 600,000 m³/h
- Pressure ratio up to 3.5
- Impeller diameter up to 2,240 mm
- Driver of your choice

Features

- Highest aerodynamic efficiency
- Minimum cooling water requirements
- Modular design principle
- Standardized components
- Wide range of proven aerodynamic impeller designs
- Flow control via inlet guide vane unit, variable diffusor guide vanes, speed control or combinations
- Backward curved impellers or radial tip with three-dimensional blades
- Excellent wear resistance over the complete impeller
- Maintenance friendly design
- OEM packages with Siemens steam turbine (SST™) available



STC-SOL

(formerly known as SL series)

from 15,000 up to 400,000 m³/h

The STC-SOL (SL) is a single-stage centrifugal compressor with open-form impeller, with radially ending blades. The impeller is mounted between the bearings. Especially designed for coke gas service.


Technical data

- Flow rates from 15,000 up to 400,000 m³/h
- Pressure ratio up to 1.45 (coke gas service)
- Impeller diameter up to 1,800 mm
- Driver of your choice

Features

- Impeller being mounted between bearings
- Minimal radial loading
- Modular design principle
- Standardized components
- Wide range of proven aerodynamic impeller designs
- Flow control via inlet guide vane unit or speed control
- Maintenance friendly design
- OEM packages with Siemens steam turbine (SST™) available
- Dual drive option available (Electric motor + SST™)





STC-SOR

(formerly known as R series)

from 600 up to 360,000 m³/h


The STC-SOR (R) is a single-stage centrifugal turboblower with closed impeller in fabricated, modular design allowing optimum adaption to nearly all process requirements.

Technical data

- Flow rates from 600 up to 360,000 m³/h
- Pressure ratio up to 1.7
- Impeller diameter up to 2,240 mm
- Driver of your choice

Features

- Large variety of impellers, casings and materials
- Various shaft seal systems
- Different bearing versions and lubrication systems
- Flexibility in direction of rotation and discharge nozzle
- OEM packages with Siemens steam turbine (SST™) available



STC-GO

(formerly known as SFNG, SFOG or SFPG series)

from 5,000 up to 300,000 m³/h


The STC-GO is an integrally geared single-stage centrifugal compressor with open-form, overhung impeller. The impeller is mounted directly onto the high-speed shaft of the gearbox. If required, this machine type is designed according to API-standards.


Technical data

- Flow rates from 5,000 up to 300,000 m³/h
- Pressure ratio up to 3.5
- Impeller diameter up to 1,120 mm
- Driver: Electric motor

Features

- Highest aerodynamic efficiency
- Minimum cooling water requirements
- Modular design principle
- Standardized components
- Integrated lube oil supply system
- Wide range of proven aerodynamic impeller designs
- Flow control via inlet guide vane unit, variable diffusor guide vanes, speed control or combinations
- Backward curved impellers or radial tip with three-dimensional blades
- Excellent wear resistance over the complete impeller
- Maintenance friendly design





STC-STO

(formerly known as ECM = Expansion Compression Module)

from 15,000 up to 150,000 m³/h

The STC-STO is an integral turbocompressor/steam turbine-unit with single shaft design. This compact design – impeller and turbine wheel are supported on a single rotor support stand – ensures very low steam consumption, high efficiency and minimum space requirements.

Technical data

- Flow rates from 5,000 up to 150,000 m³/h
- Pressure ratio up to 3.5
- Impeller diameter up to 900 mm (compressor)
- Driver: integrated Siemens steam turbine (SST™)

Features

- Very low steam consumption
- Highest aerodynamic efficiency
- Minimum cooling water requirements
- Modular design principle
- Integrated lube oil supply system
- Wide range of proven aerodynamic impeller designs
- Flow control via inlet guide vane unit or speed control
- Backward curved impellers with three-dimensional blades
- Excellent wear resistance over the complete impeller
- Maintenance friendly design



Fields of application

Siemens pre-designed turbo compressors are designed and manufactured for pretentious industrial applications:

Petrochemicals and Refineries

- SRU (Sulfur recovery units)
- Evaporation (e.g. Oil Sands – SAGD/Effluent treatment)

Chemicals

- Fertilizer (Sulfuric Acid)
- Evaporation
- MA/PA
- MMA
- Formaldehyde
- Chlorine gas (wet)
- Various chemical processes

Metallurgy

- Coke oven gas
- Sulfuric acid
- Converter blower
- Ore roasting & processing

The design of pre-designed turbo compressors meets the customer's requirements, such as:

- Highest availability
- Lowest operating costs
- Corrosive gases
- Optimized controls

A full range of World Class Turbocompressors

Siemens offers a full range of pre-designed turbocompressors to meet the needs of the metallurgical, oil and gas and chemical industries. Single stage compressors and blowers with separate gearbox or integrated gearbox can be matched with a range of drivers – steam turbine or electric driver – in a solution to match each unique customer. One of the leading turbo machinery manufacturers with over 100 years of experience and continuous development, and a fleet of more than 4,000 installed turbocompressors and blowers; we are a prime partner for your business.

A wide range of products and a wealth of experience

With our unrivalled competence in compressor unit solutions from a single source, Siemens offers a comprehensive range of pre-designed turbo compressor up to 600,000 m³/h, with the flexibility to address the specific requirements for your application (Siemens Turbo-compressors – STC™).

Our standard units with modular design ensure low investment costs and shortest delivery times.

Metallurgical, chemical and petrochemical plants as well as refineries are amongst the most common applications for our compression solutions.

We strictly adhere to the guidelines laid down in the quality standards ISO 9001 and ISO 14001. Not only the turbo-compressors and blowers, but also associated field-proven high-tech products are available in the Siemens range. These include steam turbines and electric drivers, instrumentation and controls, as well as auxiliary and ancillary systems.



Type	Volume flow (m ³ /h)	100,000	150,000	200,000	250,000	300,000	350,000	400,000	450,000	500,000	550,000	600,000	
STC-SOF	15,000 – 600,000 m ³ /h	[Bar chart showing range from 100,000 to 600,000 m³/h]											
STC-SOL	15,000 – 400,000 m ³ /h	[Bar chart showing range from 100,000 to 400,000 m³/h]											
STC-SOR	600 – 360,000 m ³ /h	[Bar chart showing range from 600 to 360,000 m³/h]											
STC-GO	5,000 – 300,000 m ³ /h	[Bar chart showing range from 5,000 to 300,000 m³/h]											
STC-STO	5,000 – 150,000 m ³ /h	[Bar chart showing range from 5,000 to 150,000 m³/h]											

Published by and copyright © 2010:

Siemens AG
Energy Sector
Freyeslebenstrasse 1
91058 Erlangen, Germany

Siemens AG
Energy Sector
Oil & Gas Division
Wolfgang-Reuter-Platz
47053 Duisburg, Germany

Siemens Industrial Turbomachinery, Inc.
10730 Telge Road
Houston, Texas 77095, USA

Siemens Turbomachinery Equipment GmbH
Hessheimer Str. 2
67227 Frankenthal, Germany

Phone: +49 6233/85-1140
Fax: +49 6233/85-2139
e-mail: compressors-frankenthal.energy@siemens.com

Oil & Gas Division
Order No. E50001-G420-A118-V1-4A00
Printed in Germany

Dispo 34806, c4bs 7488, 7490 P WS 11102.

All rights reserved.
Subject to change without prior notice.
Printed on paper treated with chlorine-free bleach

Trademarks mentioned in this document are
the property of Siemens AG, its affiliates, or their
respective owners.

The information in this document contains general
descriptions of the technical options available, which
may not apply in all cases. The required technical
options should therefore be specified in the contract.