

SIEMENS

Ingenuity for life

SGT-A35 RB gas turbine

Formerly Industrial RB211-GT30

The SGT-A35 RB continues the Industrial RB211 gas turbine legacy, introducing its latest evolution packaged with Dresser-Rand's oil and gas expertise. With a power output of up to 38 MW, the SGT-A35 RB offers best-in-class power density in an offshore package that is easy to maintain.

Important features


- 34 MW or 38 MW power output
- Lightweight gas turbine integrated with the compact Dresser-Rand package
- Compact package minimizes footprint and topside weight to lower capital investment
- Compliant with oil and gas application requirements, including those of Floating Production, Storage and Offloading (FPSO) vessels

Customer service and maintenance

- Ease of maintenance and maximum uptime through optimal access to key systems
- Fast core engine exchange
- Regional service support, 24/7 global help desk

Key benefits

- Highest power density in its class, with up to 38 MW output
- Lightweight, compact modular package
- Evolution of trusted Industrial RB211, enhanced with proven components
- Optimized for hot climate performance
- No "hot lockout" by inherent design, restart immediately following a shutdown
- Fast engine change to maximize uptime
- Mechanical drive or 60/50 Hz electrical generation without gearbox
- Designed for maximum availability and lower OPEX



Lightweight architecture of the SGT-A35 RB gas turbine

- 1** Two gas generator variants are matched to a lightweight, aeroderivative free power turbine.
- 2** The free power turbine can direct-drive a 2-pole A/C generator at 60 Hz or 50 Hz without gearbox. It can also operate in mechanical drive.
- 3** The 38 MW variant utilizes a compressor zero-stage to increase the power output with the same firing temperature.



Power generation package for flexible, efficient offshore power



Offshore package with single-lift capability and high availability

Frequency	Model	Power (MW)
50 Hz	SGT5-8000H	425 MW
	SGT5-4000F	329 MW
	SGT5-2000E	187 MW
60 Hz	SGT6-8000H	310 MW
	SGT6-5000F	250 MW
	SGT6-2000E	117 MW
50 or 60 Hz	SGT-A65 TR	53 to 66 / 54 to 62 MW
	SGT-800	48 to 54 MW
	SGT-A45 TR	39 to 44 MW
	SGT-750	40 / 41 MW
	SGT-700	33 / 34 MW
	SGT-A30 RB SGT-A35 RB	27 to 33 / 28 to 34 MW
	SGT-600	24 / 25 MW
	SGT-400	13 to 14 / 13 to 15 MW
	SGT-300	8 / 8 to 9 MW
	SGT-100	5 / 6 MW
SGT-A05 AE	4 to 7 MW	

Gas turbines from 4 to 425 MW

Power generation

The SGT-A35 RB can drive a 2-pole (no gearbox) or 4-pole A/C generator. Its aeroderivative architecture and free power turbine is designed for operational agility and fast, stable response to large load variations.

- Single-lift package
- Compact footprint
- No "hot lockout"

Mechanical drive

The SGT-A35 RB delivers a shaft output of up to 38.1 MW in mechanical drive. The drive shaft design speed is 3,429 rpm.

- Single-lift package
- High starting torque
- Variable output speed, up to 105% for continuous operation
- Configured to order with pre-engineered features

Trusted technology, game-changing performance

- Evolved from the reliable Industrial RB211 gas turbine, proven in over 800 units and 37 million hours of service
- Packaged with Dresser-Rand's oil and gas expertise from more than 1,000 aeroderivative packages
- 10% more power than its predecessors
- Over 90% of ISO power output retained at 30° C
- Lightweight free power turbine with Trent components proven in flight, marine and industrial service
- 38 MW with compressor zero-stage, same firing temperature

Nominal rating	34 MW		38 MW	
	15° C	30° C	15° C	30° C
Mechanical drive (3,429 rpm)				
Shaft power output	33.7 MW	30.8 MW	38.1 MW	33.3 MW
Shaft thermal efficiency	39.1%	38.3%	40.3%	39.1%
60 Hz electrical generation				
Power output A/C	33.2 MW	30.3 MW	37.4 MW	32.6 MW
Simple cycle efficiency	38.5%	37.8%	39.7%	38.4%
50 Hz electrical generation				
Power output A/C	32.2 MW	29.7 MW	36.6 MW	32.4 MW
Simple cycle efficiency	37.5%	36.8%	38.7%	37.6%
Power turbine speed	3,000 – 3,600 rpm			
Fuel type	Dual (gas & liquid)			

Published by
Siemens AG 2017

Power and Gas Division
Distributed Generation
Freyeslebenstrasse 1
91058 Erlangen, Germany

Article No. PGDG-T10036-00-7600
Printed in Germany
Dispo 34806
TH 566-170381 FS 0417

Subject to changes and errors.
The information given in this document only contains general descriptions and/or performance features which may not always specifically reflect those described, or which may undergo modification in the course of further development of the products. The requested performance features are binding only when they are expressly agreed upon in the concluded contract.

Note: Nominal performance shown.
Performance guarantees are only provided in individual project proposals based on specifications given. Nominal performance shown referred to sea level, 60% relative humidity, natural gas fuel, zero installation losses. Power generation data includes the A/C generator. Mechanical drive data excludes the driven equipment.