



SIEMENS

With
Rolls-Royce
Aero Engine
Technology

The Industrial 501-K Gas Turbine

[siemens.com](https://www.siemens.com)



Industrial 501-K gas turbine

Dependable, flexible design for onshore and offshore applications

More than 1,600 Industrial 501-K gas turbines have been supplied for industrial use to 500 customers in 40 countries, accumulating an impressive 110 million operating hours since its introduction in 1963.

Today, these engines are delivered to our customers through a network of distributors who incorporate the engine into complete generator sets (both stationary and mobile) or mechanical drive units. All Siemens distributors are carefully chosen for their engineering and manufacturing capabilities and commitment to adhere to Siemens standards for quality and delivery.

Industrialized Aero-derivative

The Industrial 501-K is an aero-derived engine based on the T-56 turboprop, which is recognized for its reliability and durability in the Lockheed Martin C-130 Hercules transport, E2C Hawkeye, P-3 Orion and other widely used aircraft. Designed for use in power generation and oil & gas applications, features of the Industrial 501-K gas turbine include:

- Lightweight modular construction
- Ease of field repair
- Virtually limitless starts and stops
- Wide range of fuels in any environmental condition
- High electrical and cycle efficiency

Industrial 501 Options for Power Generation Applications

The Industrial 501-K gas turbine provides electrical power output between 3.9 and 6.4MW for applications such as co-generation, offshore platforms and emergency power. The single-shaft, designated as Industrial 501-KB5S/KB7S, is designed for electrical power generation and fixed speed mechanical drive applications. The steam injected, single-shaft Industrial 501-KH provides 6.4MW of power at efficiency levels unprecedented for gas turbines of this size. Also, the amount of steam can be adjusted to meet varying process steam or electrical requirements, depending on the application.

Industrial 501 Options for Mechanical Drive Applications

A two-shaft version, designated as Industrial 501-KC5/KC7 is ideal for driving pumps with centrifugal compressors, which require a wider operating speed range. Multiple versions of the engine produce between 4 and 5MW for use in pipeline transmission, gas storage and withdrawal, field gas compression and crude oil pumping.



“All Siemens distributors are carefully chosen for their engineering and manufacturing capabilities and commitment to adhere to Siemens standards for quality and delivery.”

Increased operating benefits

Improved performance through advanced engineering

The Industrial 501-K engine is designed to operate on a wide variety of fuels. Fuels include, but are not limited to, natural gas, liquid fuel (typically DF-2 or equivalent) and mid to low BTU gas fuels. Fuel system options also include dual fuel, steam and water injection. Dry Low Emissions (DLE) technology is also available.

In addition to its fuel flexibility, it accommodates a wide variety of customer requirements. The compact design of this engine also permits application versatility and ease of removal and replacement. The Industrial 501-K measures less than 2.7 meters (8 feet) long and weighs less than 766 Kg (1,690 pounds).

The Industrial 501-K is proven to operate in various challenging conditions and locations around the world including the North Sea, West Africa, Siberia, Brazil, Alaska, South East Asia and the desert regions of the Middle East. The Industrial 501-K engine has been shock qualified to Mil-S-901C, which makes it particularly suitable for areas with frequent or severe seismic activity.

Advanced Engineering

- Core engine commonality of all five Industrial 501-K variants
- All Industrial 501-K engines are built to meet stringent industry standards including ISO 9001 and AS9100
- Anti-corrosion coatings for offshore services
- Full power available within 60 seconds from all conditions, including hot restarts, with no need to go to an idle condition


- Black Start capability
- Modular gas turbine configuration optimizes spares requirements, minimizes cost of ownership and simplifies engine maintenance

Efficiency and Low Emissions Options

- Three combustion systems are available, based on customer need
- Standard combustion system can operate on liquid or gas fuel
- Wet Low Emissions combustion systems utilize nozzle steam or water
- Dry Low Emissions combustion system achieves better than 25vppm NOx and 50vppm CO
- Class leading efficiency for both simple cycle and combined heat and power operations

Reliable, Easy Installation and Maintenance

- Simple, inexpensive to maintain
- Rugged, reliable performance with up to seven years baseload duty between full overhaul
- Over 98% demonstrated availability/reliability
- Lightweight, aero-derivative, industrial design is easy and economical to transport and install
- Engine change-out in as little as 12 hours, and many repairs can be made at the site
- Ideal for remote, inaccessible locations and performance proven in many extreme environments



Packaged for success

Package features for all applications

Lubricating Oil System

- Turbine synthetic lube oil system may be either integrated with or separated from the driven equipment, depending upon customer requirements
- Main lube pump is driven off the engine accessory gearbox for normal operation and shutdown
- Oil system components are skid-mounted and designed to industry standards for mechanical drive
- Optional heaters/coolers to meet the climate needs of the application

Fuel System

- On-skid fuel system includes all components needed to control fuel during start up and operation
- Operates on natural gas, liquid, dual fuel, and low BTU gas with steam and water injection

Low Emissions

- Dry Low Emissions (DLE) system available on Industrial 501-K variants; both power generation and mechanical drive applications

Start Systems

- Several types of start systems are available depending on customer requirements
- Overrunning clutch disengages when self-sustaining speed is reached

Baseplate

- Sturdy, but small, lightweight footprint
- Design allows easy access for maintenance
- Jib boom provides easy installation or removal of gas turbine

Electrical

- Available to meet local standards as needed

Air Intake System

- Provides clean, uniform airflow to the gas turbine
- Includes filter assembly, silencer and flow direction geometry
- Site-specific design minimizes disruption of inlet air
- Filtration systems are available to handle extreme environments – arctic cold, salt water spray, severe heat and dust
- Single to multiple stages handle offshore, coastal and inland sites

Gas Turbine Enclosure

- Acoustic enclosures meet a wide range of requirements and environments
- Factory-completed enclosure can house all auxiliary equipment on engine skid, with piping and wiring completed and tested at the factory
- Completed enclosures shipped with connections intact for simplified installation and commissioning

Water Wash System

- Maintains performance by preventing build-up of contaminants in the engine compressor
- Pump or compressed air system includes storage tanks, pressure gauges, valves and piping



“Twenty-four hours a day, seven days a week, expert field service engineers work to install, maintain and service customer equipment.”

Complete customer care through the life of the product

The global infrastructure of Siemens and its distributors provides customers with the support they need at any time, anywhere in the world. Service centers in every region of the world, combined with a responsive spares program and expert field service representatives, all unite to provide a comprehensive system of service to keep our customers' equipment running reliably.

Engine Lease

Engine lease programs are as varied as our customers' needs. Whether for routine maintenance, or in an emergency, engines can be made available to minimize disruptions to daily operations.

Spares


A worldwide spares inventory allows parts to be delivered anywhere in the world, and as the original equipment manufacturer, Siemens is committed to supplying only the highest quality parts, whether new or refurbished.

Field Service

Twenty-four hours a day, seven days a week, expert field service engineers work to install, maintain and service customer equipment. Their high level of skill allows them to respond rapidly and effectively to a range of situations that may arise. They also provide training and equipment monitoring. Field service is provided by the distributor network or Siemens.

Engineered Solutions

Upgrades to existing equipment are an attractive option for many customers, and a dedicated team of engineers and project managers work to ensure that the customer's equipment is providing the most power, efficiency and reliability possible. There are currently seventeen different upgrades available for the Industrial 501-K engine. Upgrades include a conversion to Dry Low Emissions (DLE), dual fuel conversion, and more.



Industrial 501-KB7S
gas turbine



A global network

Industrial 501-K distributors and Siemens maintenance, repair and overhaul centers

Our customers may be located in diverse regions around the world, but they all have one thing in common. They all require timely and accurate support to purchase, install and maintain their Industrial 501-K engines and equipment. That's why we continually invest in our global infrastructure from distributors to repair and overhaul facilities.

Industrial 501-K Distributors

Several distributors, backed by the engineering and support of Siemens, are available globally to provide Industrial 501-K equipment and support to your operation.

Repair and Overhaul Facilities

Siemens repair and overhaul facilities are strategically placed around the globe to provide rapid turnaround on all repair and overhaul services.

Business Locations

Siemens aero-derivative gas turbine offices are located globally to provide direct contact with our customers and more effectively meet the needs of those in both the oil & gas and power generation industries.

Packagers:

Centrax Limited, Gas Turbine Division (Europe)

Shaldon Road, Newton Abbott
Devon TQ12 4SQ England
+44 1626 358 000

OnPower, Inc. (North America)

3525 Grant Drive, Suite A
Lebanon, Ohio 45036
+1 513 228 2100

Hitachi Zosen Corporation (Japan)

7-89 Nanko-kita 1-Chome
Sumineo-ku, Osaka 559-8559 Japan
+81 6 6569 0209

IHI Jet Services (Japan)

Toyosu IHI Building
1-1, Toyosu 3-chome
Koto-ku, Tokyo 135-8710 Japan
+81 3 6204 7718

Kobe Steel, Ltd. (Japan)

1-3, 4-chome, Bingo-machi
Chuo-ku, Osaka 541-8536 Japan
+81 6 6206 6518

Tominaga & Co., Ltd. (Japan)

2-6-3, Nihonbashi Honcho
Chuo-Ku, Tokyo 103-0023
+81 3 3639 5360



“We continually invest in our global infrastructure from distributors to repair and overhaul facilities.”



- Distributors
- Repair and Overhaul Facilities
- Aero-derivative Business Locations

USA contact details

Siemens Energy Inc.
201 S. Capitol Ave
Suite 910
Indianapolis, In 46225
USA

Phone: +1 (317) 677-1340
Fax: +1 (317) 677-1341

Published by and copyright © 2014:
Siemens AG

Power and Gas
Freyeslebenstrasse 1
91058 Erlangen, Germany

For more information, please contact
our Customer Support Center.
Phone: +49 180 524 70 00
Fax: +49 180 524 24 71
(Charges depending on provider)
E-mail: support.energy@siemens.com

Order No. E50001-G430-A128-X-4A00
WS 1114

Printed on elementary chlorine-free
bleached paper.

All rights reserved. Trademarks
mentioned in this document are the
property of Siemens AG, its affiliates, or
their respective owners. Product Mark
501 is a trademark of and used under
license from Rolls-Royce plc.

Subject to change without prior notice.
The information in this document
contains general descriptions of the
technical options available, which may
not apply in all cases. The required
technical options should therefore be
specified in the contract.

